AGRU-8

HIGHEST ACCURACY & LOWEST COST



SF₆Gas RecoveryUnit

AGRU-8

- Storage no included. Two Options:
 - + 300I- ASME Tank with weight Scale
 - +Horizontal 3 cylinder storage with evaporator and Scale
- Vacuum Capacity:
 - $+30m^3/h$ (60Hz 110V) <1mbar --> 40 m^3/h (Upgrade)
 - $+25m^3/h$ (50Hz 220V) <1mbar --> 35 m^3/h (Upgrade)
- -Evacuate pressure < 0,5 mbar
- Weight: 950 lbs 432 Kg
- Dimensions: 74"x45"x58" 1900x1140x1470 mm (H x W x D)

Optional:

PLC control touch screen, Tank heater, SS tubing and hoses, increase vacuum compressor and pump.



www.amperis.com



⊠ Contact

+T [+34] 982 20 99 20 | F [+34] 982 20 99 11 info@amperis.com | www.amperis.com

We developed the AGRU-8 for our customers whofound they needed more storage and recoverycapacity than smaller handcart mounted units, the AGRU-8 is available without the bulk and high price of a large skid or trailer mounted unit. The equipment is designed for use in field service of insulated metal clad switchgear, bus ducts and individual circuit breakers. The AGRU-8 SF₆ Gas Servicing Cart shall be fully assembled on a two-wheeled heavy-duty handcart, which shall be sufficiently braced to minimize vibration.

Handcart will be complete with lifting eye, hosehook and power cable storage.

Funtions:

- Recover, purify and store SF₆ Gas from the switchgear to the storage tank.
- Evacuation:
- Service hoses < 0.5 mbar
- SF6 Gas cart down < 0.5 mbar
- Air and moisture from the switchgear < 0.5 mbar
- Purify SF6 Gas by recirculating through the filter system:
 - (D1) & (D2)- Dryer Filter Contains activated alumina to aid in the drying and purification of SF₆ Gas.
 - (P1) Purification Filter Contains Molecular Sieve 5X to remove arcing by-products.
 - (F1) Particulate Filter Will filter all particulate matter down to 0.1 micron nominal.
- Pressure regulated recharging of SF₆ Gas to the switchgear from the storage tank.
- Evacuate SF₆ Gas from the cart to an external storage tank for maintenance purposes.



Features:

- Mounted of a convenient hand cart with 10" (400mm) pneumatic tires for ease of movement in gravel switchyard environments.
- Very easy to operate only two valves to switchoperating modes.
- High pressure, direct-drive oil-less compressor with 1000:1 compression ratio (capable of 1000psi 69 bar).
- Capable of liquid SF6 storage.
- Purifies, dries and filters to 0.1 microns during recovery and re-pressurization.
- Filters are easily changed without disconnecting any tubing or using any special tools.
- Auxiliary connection allows for infinitely expandable storage through use of external tanks.
- Comes complete with 9.8ft / 3m hoses and power cable.
- Colour change moisture indicator to monitor moisture in gas.
- Mounted on a cart with casters and rack for storage up to three SF6 storagebottles. 156 kg with four bottles or 300l (300 kg) with the tank.

Applications:

- Recover and purify SF₆.
- Evacuate air and moisture prior to filling.
- Consolidate SF6 cylinders.
- Store SF₆ in liquid state in onboard storage or auxiliary bottles.
- Regulated filling of SF6 equipment.
- Purification of SF6 (removes particles, moisture, and SF6 decomposition products).



GIS





+T [+34] 982 20 99 20 | F [+34] 982 20 99 11 info@amperis.com | www.amperis.com



AGRU-8 Specifications

Type Portable SF₆ Gas Recovery Unit.

Physical specifications 58" (1470 mm) Wide x 45" (1140 mm) Deep x74" (1900 mm) //950 lbs. (432kgs.).

Input power 110Vac/60Hz - 220Vac/50Hz - other available configuration (choose it in the order).

SF6 Compressor Three (3) High Pressure Single Stage Direct Drive Oil-less Compressors capable of producing pressures of 70 bar. Compressor motor 1/2 kW, 3450 rpm.

Compressorhas metal valve construction. 6.6 m³h⁻¹ displacement (60Hz).

Suction pressure regulator One Suction pressure regulator, brass body, 0-2 bar, spring

Vacuumcompessor One diaphragm type vacuum compressor, 0.24kW motor, 5 m3h-1displacement (60 Hz), ultimate vacuum: 20 mbar. (Optionally available - Scroll

vacuumcompressor with ultimate vacuum whilst recovering SF₄ of <1 mbar - allows 99.9% SF₆ gasrecovery).

Equalization circuit One Equalization circuit, to allow for high-pressure restarts of the compressor.

Dischargecheckvalve Nine discharge check valve, brass, prevents high pressure going back to compressor whenperforming a low-pressure equalization.

Condenser One High efficiency, 4-pass, air-cooled SF6 condenser to aid in liquification of SF6 at higherambient temperatures.

Discharge pressure One High discharge pressure switch set to automatically shut unit down when it reaches maximum allowable pressure.

VacuumPump Motor: 1.1 kW, 1750 RPM, TEFC electric motor. Optionally available 40 m³h-1 vacuum pump.

Displacement:

- 30 m³/h (60Hz - 110V)

- 25 m³/h (50Hz - 220V)

Blank off pressure: 0.08 mbar.

Pump also includes: positive antisuckback valve, isolation valve, gas ballast, and automatic oil return system.

Storage Tank Cylinders secured onto a tray andmanifold, in order to store up to 156kgs. of SF6 in liquid form indefinitely, at ambient temperatures of less than 114°F

(45.5°C), without the need for refrigeration. The AGRU-8 shall come equipped with anexternal storage port, to which any SF₆ Gas cylinder or tank rated at 40 bar minimum) can be attached to allow for unlimited storage of SF₆. All storage tanks shall include an isolation valve, and an approved safety

relief valve.

Filters (D1) & (D2) - Dryer Pre- Filter & Filter - Contains activated alumina to aid in the drying and purification of SF6 Gas.

(P1) - Purification Filter - Contains Molecular Sieve 5X to remove arcing by-products.

(F1) - Particulate Filter - Will filter all particulate matter down to 0.1 micron nominal.

Valves Designed for pressure, temperature and flow. Bronze body with Teflon seats and seals, quarter turn.

Pressure Gauges One (4" stainless steel) for equipment pressure (compound).

One (4" stainless steel) for discharge pressure.

Vacuum Gauge 0-50 mbar for vacuum system.

Hoses

Pressure Regulator One Pressure Regulator, Brass body, 0-7bar spring, to allow for saferegulated filling of SF6 equipment.

Two Permeation Rubber Resistant Hoses: 12 mm I.D. X 4.5 meter. Long, complete withquick disconnect self-sealing end fittings. Hoses will be suitable

for system pressure, temperatureand flow.

AGRU-8 - Optional Upgrades and Accessories

Stainless Steel (SS) Tubing Unit can be supplied with stainless steel tubing replacing the standard copper tubing.

Stainless Steel Hoses Unit can be supplied with stainless steel hoses replacing the standard rubber hoses.

Storage Tank - An optional SF6 Cylinder, Size H - 52 kg., with CGA 590 valve connection with no check valve, 99.9% drycan be provided. The AGRU-8 has a capacity

to hold 3 bottles on board to give a total storage capacity of 156 kgs.

- An optional SF6 Storage Tank, 300 litres (300 kgs.), can be supplied to increase the storage capacity of the AGRU-8.

Storage TankHeater 300 W storage tank heater. Heater comes with its own power cable andhas a thermostat preset at 125 °F (52 °C) and is protected from overheating by

a thermal cut-off. Theheater maintains an even temperature for a constant positive pressure that speeds up the charging process.

ElectronicWeighScale An optional electronic cylinder weighing scale to monitor the filling of the SF6 cylinders. Weigh scalesystem comes complete with an adjustable

maximum weight set point and includes a weighing systemand cylinder mounting bracket.

DN-20 Style Quick Connections Unit can be supply with DN-20 style quick connections on equipment and hoses.

Increase Hose Length Unit can be supply with 6m. hoses instead of 3m.

PLC Control Touch Screen Unit can be supply with PLC control Touch Screen with Automatic or Manual Valve Control instead of conventional panel control.

Increase Vacuum Compressor/Pump Unit can be supply upgrading ultimate pressure of vacuum compressor < 1mbar (instead of 20mbar). Also, unit can be supply upgrading vacuum pump to

40 m³h⁻¹(60 Hz).

AGRU-8-Spare Parts

Filter D-1 Dryer Filter – recommended to change each 50 hours of compressor work.

Filter P-1 Purification Filter – recommended to change each 50 hours of compressor work.

Filter F-1 Particulate Filter – recommended to change each 50 hours of compressor work.

Vacuum Pump Oil Vacuum pump oil level has to be checked each time you turn it on. Available in two quantities: 946 ml or 3780 ml.